

Garant

Dados do pedido

Número do pedido	469190 200/1
GTIN	4045197519252
Classe de artigo	41H

Descrição

Modelo:

Sturdy frame of high quality special casting; hammer finish. 3 sides Vee ground, 1 side flat. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square. Accuracy grade 1 has insulated handles on the housing and protective glass cover over the vials.

Adjustment of the longitudinal vial:

An adjustment screw allows the longitudinal vial to be reset to the 0 position easily and without play, with no need for disassembly.

Norma:

DIN 877

Descrição técnica

Classe de precisão	1
Leitura	0,02 mm/m
Largura palmilha	40 mm
Comprimento da palmilha	200 mm
Norma	DIN 877

embalagem	caixa estável
Calibração	H1
Tipo de produto	Nível de bolha de ar

Prestações de serviços

CalibraçãoNível de água de quadro Precisão 0,02	026600 0,02
---	-------------