



Dados do pedido

Número do pedido	365023 110
GTIN	4045197563200
Classe de artigo	32P

Descrição

Modelo:

- **Quick adjustment of the movable jaws.**
- **Jaws through hardened and ground.**
- **Time-consuming cranking not necessary.**
- **Precise clamping due to long flat guide.**
- **Clamping of component with just one hand.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**
- **With two side support faces.**
- **Positive locking.**

Descrição técnica

Código de cor para acessório adequado	Torno de bancada BM azul
Altura total c	82 mm
Peso	9,5 kg
comprimento total máximo L ₄	510 mm
Largura do mordente A	110 mm
Área de aperto b	130 mm
Altura do mordente C	32 mm
Largura do corpo base B	112 mm

Comprimento do corpo base a	280 mm
Tipo de produto	Torno de bancada para perfuradoras

Acessórios

batente Tipo 1	365028 1
Calha de guia para o n.º 365023	365025