

**BENNING**

## Dados do pedido

Número do pedido	473260 DUTESTPRO
GTIN	4014651501560
Classe de artigo	47A

## Descrição

**Modelo:**

High-resistance and low-resistance continuity testing with 3-stage LED display and sound intensity of the test buzzer. External voltage and polarity display, single-pole and contactless phase testing. The buzzer sound intensity (3-stage/OFF) and illumination intensity (4-stage) are adjustable. With high-power LED torch.

**Norma:**

IEC / DIN EN 61010-1, (DIN VDE 0411-1).

## Descrição técnica

Verificação da continuidade	0 – 0,1 / 1 / 10 (LED); 0 – 0,1 (besouro) kΩ
Indicação da polaridade	LED +/–
Indicação da passagem	LED de 3 níveis
Indicação da tensão externa CA/CC	6 – 400; som de aviso pulsante V
Designação do fabricante	DUTEST PRO

verificação de fases unipolar	através de um cabo de medição de 4 mm / sem contacto através de um detetor
Número de pilhas incluídas	3
Pilhas/baterias incluídas no n.º de artigo	081561 LR6
Alimentação de energia	A pilhas
Tipo de produto	Detetor de corrente e continuidade

---

## Acessórios

Pilhas alcalinas de manganês Tamanho internacional LR6	081561 LR6
--	------------