

Mitutoyo

Dados do pedido

Número do pedido	493510 A3010
GTIN	
Classe de artigo	44C

Descrição

Modelo:

Projector for the exact transillumination and incident light inspection of small to medium-sized components. **Universal tool** for use in production, laboratory, inspection, and grinding shop.

- **Standard lens 10×. 20× and 50× lenses available as optional accessories. Maximum distortion of the lenses 0.2 %.**
- **Vertical, rotating 315 mm cross-hair screen with built-in digital angle display, switching for reading in degrees or decimal.**
- **The telecentric lighting system guarantees a vertical and even illumination of the image field.**
- **Halogen transillumination and incident illumination integral in the housing.**
- **Sturdy coordinate measurement table, with quick adjustment in both axes.**
- **Built-in digital display (with data output) guarantees reliable, error-free measuring.**
- **For measuring lengths, angles, curves, and radii.**

Descrição técnica

Altura	1080 mm
--------	---------

Largura	550 mm
Peso	140 kg
Faixa de medição do eixo y	100 mm
Faixa de medição do eixo x	200 mm
Leitura	0,001 mm
Comprimento	760 mm
peso máximo da peça	8 kg
Ø do monitor	315 mm
Designação do fabricante	PJ-A3010F-200
Alimentação de energia	A energia elétrica
Tipo de produto	Projetor de perfil