

**RIDGID**  
Peddinghaus

## Dados do pedido

Número do pedido	967170 100
GTIN	
Classe de artigo	93R

## Descrição

### Modelo:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**Sturdy** design.

## Descrição técnica

Sentido de abertura	com abertura para a frente
Peso	6 kg
Largura de aperto	125 mm
Profundidade de aperto	65 mm
largura do mordente	100 mm
Série	Matador Multiplus
Tipo de produto	Torno de bancada paralelo

## Acessórios

Par de mordentes de torno de bancada magnéticos Alumínio, perfilado largura do mordente 100	967722 100
Par de mordentes de torno de bancada de metal leve com molas de aperto largura do mordente 100	967711 100
Par de mordentes de torno de bancada magnéticos Poliuretano, com nervuras largura do mordente 100	967728 100
Par de mordentes de torno de bancada magnéticos Revestimento de alumínio/fibra, liso largura do mordente 100	967724 100
Par de mordentes de torno de bancada magnéticos Alumínio, prisma largura do mordente 100	967723 100
Par de mordentes de torno de bancada magnéticos Borracha, lisa largura do mordente 100	967727 100
Placa de base para torno de bancada	967330
Par de mordentes de torno de bancada magnéticos Feltro, liso largura do mordente 100	967726 100
Par de mordentes de torno de bancada magnéticos Poliuretano, prisma largura do mordente 100	967729 100
Par de mordentes de torno de bancada magnéticos Alumínio, liso, standard largura do mordente 100	967721 100
Placa de base para torno de bancada, bambu Tamanho 300X250	967328 300X250