

RIDGID
Peddinghaus

Dados do pedido

Número do pedido	967170 120
GTIN	
Classe de artigo	93R

Descrição

Modelo:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

Sturdy design.

Descrição técnica

Sentido de abertura	com abertura para a frente
Profundidade de aperto	80 mm
Peso	10 kg
Largura de aperto	150 mm
Os mordentes de aperto para tubos apertam tubos com um \varnothing exterior	1/8 – 4 polegada
largura do mordente	120 mm

Série	Matador Multiplus
Tipo de produto	Torno de bancada paralelo

Acessórios

Placa de base para torno de bancada, bambu Tamanho 300X250	967328 300X250
Par de mordentes de torno de bancada magnéticos Revestimento de alumínio/fibra, liso largura do mordente 120	967724 120
Placa de base para torno de bancada	967330
Par de mordentes de torno de bancada magnéticos Alumínio, perfilado largura do mordente 120	967722 120
Par de mordentes de torno de bancada de metal leve com molas de aperto largura do mordente 120	967711 120
Par de mordentes de torno de bancada magnéticos Alumínio, prisma largura do mordente 120	967723 120