

**RIDGID**  
Peddinghaus

## Dados do pedido

Número do pedido	967170 160
GTIN	
Classe de artigo	93R

## Descrição

### Modelo:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**Sturdy** design.

## Descrição técnica

Sentido de abertura	com abertura para a frente
Largura de aperto	225 mm
Profundidade de aperto	120 mm
Peso	25 kg
Os mordentes de aperto para tubos apertam tubos com um $\varnothing$ exterior	1/8 – 6 polegada
largura do mordente	160 mm

Série	Matador Multiplus
Tipo de produto	Torno de bancada paralelo

## Acessórios

Par de mordentes de torno de bancada magnéticos Alumínio, prisma largura do mordente 160	967723 160
Par de mordentes de torno de bancada magnéticos Alumínio, perfilado largura do mordente 160	967722 160
Placa de base para torno de bancada, bambu Tamanho 300X250	967328 300X250
Par de mordentes de torno de bancada magnéticos Revestimento de alumínio/fibra, liso largura do mordente 160	967724 160
Par de mordentes de torno de bancada de metal leve com molas de aperto largura do mordente 160	967711 160
Placa de base para torno de bancada	967330