



Set de chei tubulare, pătrat 3/8 inch 33 buc. dimensiuni metrice / inch



Date comandă

Numărul de comandă	634711
GTIN	4018754260430
Clasa articolului	63A

Descriere

Execuție:

Părți de acționare / de conectare conform DIN 3122 / 3123; chei tubulare conform DIN 3124.
Pătrat interior / exterior conform **DIN 3120**.

Aplicație:

Pentru șuruburi cu hexagon exterior / piulițe cu filet M4 – M14, pentru șuruburi / piulițe cu filet până la 9/16 inch (mărimi americane în inch).

Material:

Oțel aliat cu crom, cromat.

Livrare:

Biți pentru chei tubulare bi-hexagonale: 16 buc. Cod 637000

Ref. 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22

Biți pentru chei tubulare bi-hexagonale: 12 buc. Cod 637100 Ref. 1/4; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4; 13/16; 7/8

Mâner tip T: 1 buc. Cod 635700

Prelungitoare: 2 buc. Cod 635400 Ref. 75; 240

Articulație cardanică: 1 buc. Cod 636200

Clichet: 1 buc. Cod 635000

Păstrare în: Cutie din plastic ABS

Înălțime: 57 mm

Pătrat de antrenare: 3/8 inch

Gamă deschidere pentru chei tubulare bi-hexagonale: 7-22 mm

Gamă deschidere pentru chei tubulare bi-hexagonale: 1/4-7/8 inch

Descriere tehnică

Gamă deschidere pentru chei tubulare bi-hexagonale	7-22 mm
Gamă deschidere pentru chei tubulare bi-hexagonale	1/4-7/8 inch
Dimensiuni deschidere chei	metric / imperial
Pătrat de antrenare	3/8 inch
Număr de piese	33
Profil de antrenare	Cheie tubulară bi-hexagonală
Lungime	413 mm
Lățime	230 mm
Înălțime	57 mm
Tip produs	Cheie tubulară

Accesorii

Bit bi-hexagonal, 3/8 inch Deschiderea cheii 18 mm	637000 18
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 3/8 Inch	637100 3/8
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 7/16 Inch	637100 7/16
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 13 mm	637000 13
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 11/32 Inch	637100 11/32
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 9/16 Inch	637100 9/16
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 5/16 Inch	637100 5/16
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 9 mm	637000 9
Prelungitor 3/8 inch Lungimea totală 240 mm	635400 240
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 15 mm	637000 15
Articulație cardanică 3/8 inch Tip 3/8	636200 3/8
Mâner tip T, 3/8 inch Lungimea totală 165 mm	635700 165
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 20 mm	637000 20
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 7 mm	637000 7
Prelungitor 3/8 inch Lungimea totală 75 mm	635400 75

Bit bi-hexagonal, 3/8 inch Deschiderea cheii 11 mm	637000 11
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 17 mm	637000 17
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 3/4 Inch	637100 3/4
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 5/8 Inch	637100 5/8
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 19 mm	637000 19
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 16 mm	637000 16
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 12 mm	637000 12
Clichet reversibil, 3/8 inch Tip	635000
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 14 mm	637000 14
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 1/2 Inch	637100 1/2
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 10 mm	637000 10
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 21 mm	637000 21
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 22 mm	637000 22
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 1/4 Inch	637100 1/4
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 11/16 Inch	637100 11/16
Bit bi-hexagonal, 3/8 inch Deschiderea cheii 8 mm	637000 8