



Set de chei tubulare, pătrat 1/2 inch, mărimi în inch 23 buc.



Date comandă

Numărul de comandă	638711
GTIN	4018754260966
Clasa articolului	63A

Descriere

Execuție:

Părți de acționare / de conectare conform DIN 3122 / 3123; chei tubulare conform DIN 3124.
Pătrat interior / exterior conform **DIN 3120**.

Aplicație:

Pentru șuruburi cu hexagon exterior / piulițe cu filet de până la 3/4 inch (măsurile americane).

Material:

Oțel aliat cu crom, cromat.

Livrare:

Chei tubulare bi-hexagonale: 17 buc. Cod 642400

Ref. 3/8; 7/16; 1/2; 9/16; 19/32; 5/8; 11/16; 3/4; 25/32; 13/16; 7/8; 15/16; 1; 1.1/16; 1.1/8; 1.3/16; 1.1/4

Mâner tip T: 1 buc. Cod 641300 Ref. 300

Prelungitoare: 3 buc. Cod 641000 Ref. 50; 130; 255

Articulație cardanică: 1 buc. Cod 641600 Ref. 1/2

Clichet: 1 buc. Cod 640100 Ref. 1/2

Păstrare în: Cutie din plastic ABS

Descriere tehnică

Profil de antrenare	Cheie tubulară bi-hexagonală
Dimensiuni deschidere chei	inch
Gamă deschidere pentru chei tubulare bi-hexagonale	3/8-1.1/4 inch

Pătrat de antrenare	1/2 inch
Număr de piese	23
Lungime	454 mm
Lățime	253 mm
Înălțime	64 mm
Tip produs	Cheie tubulară

Accesorii

Bit bi-hexagonal, 1/2 inch Deschiderea cheii 11/16 inch	642400 11/16
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1.1/8 inch	642400 1.1/8
Prelungitor, 1/2 inch Lungimea totală 255 mm	641000 255
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1.3/16 inch	642400 1.3/16
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 5/8 inch	642400 5/8
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 15/16 inch	642400 15/16
Prelungitor, 1/2 inch Lungimea totală 130 mm	641000 130
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 3/4 inch	642400 3/4
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 7/16 inch	642400 7/16
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1.1/4 inch	642400 1.1/4
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 9/16 inch	642400 9/16
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1.1/16 inch	642400 1.1/16
Mâner tip T, 1/2 inch Lungimea totală 300 mm	641300 300
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 13/16 inch	642400 13/16
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 25/32 inch	642400 25/32
Prelungitor, 1/2 inch Lungimea totală 50 mm	641000 50
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1 inch	642400 1
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 1/2 inch	642400 1/2
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 3/8 inch	642400 3/8
Bit bi-hexagonal, 1/2 inch Deschiderea cheii 19/32 inch	642400 19/32

Bit bi-hexagonal, 1/2 inch Deschiderea cheii 7/8 inch	642400 7/8
Articulație cardanică, 1/2 inch Tip 1/2	641600 1/2