

**Garant****Nástrčný klúč s 2K-zložkovou rukoväťou Haptoprene plne izolovaný, Rozmer cez steny: 10mm**

## ÚDAJE O OBJEDNÁVKE

Číslo objednávky	622492 10
GTIN	4067263116431
Trieda položky	61C

## Popis

### Prevedenie:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage. **Application:** For use at voltages up to 1000 V.

Ergonomically shaped **power grip** with easy-grip **Haptoprene** surface and an impact-resistant plastic core. The special surface structure allows transmission of high torques, even with wet or oily hands. **Blade** of chrome vanadium steel.

## Technický opis

Celková dĺžka	236 mm
Dĺžka čepele	125 mm
Výstupný profil	6-hranný nástrčný klúč