



## ÚDAJE O OBJEDNÁVKE

Číslo objednávky	957650 1500
GTIN	4260302417289
Trieda položky	9GG

## Popis

### Prevedenie:

Mobile, easy-to-carry power supply for mobile workbenches, UNI Lines etc. Diverse connections for end devices such as laptops, monitors, smartphones and small consumers. A car can even be started with a battery charge of more than 60% and a corresponding cable (not included). Possibility to charge via 230 V mains socket and DC/solar charging connection or via 12 V on-board power socket. **LiFePO4** (lithium iron phosphate) **lithium battery** with continuous power of 1500 W and maximum power of 3000 W. With integrated solar charging controller for solar charging with up to 200 Wp at 10 A. More than 4000 charging cycles possible at 80% DoD.

**Battery capacity:** 1497 Wh

**AC output:** 2 pcs. 230 V, 50 Hz, pure sine wave.

**DC outputs:** 4 pcs. USB port, 1 pc. USB-C port, 2 pcs. DC output, 1 pc. on-board power socket (12 V).

**Capacity (AH):** 58.5 Ah (25.6 V)

**Connections:** EC5 (for JumpStarter cable)

## Technický opis

Druh batérie	Lítium-fosforecnan železitý
Dĺžka	480 mm
Napätie	230 V
Šírka	190 mm

Výška	240 mm
Hmotnosť	20 kg
Kapacita	58,5 Ah
Druh produktu	Akumulátor