

**Verkt ygsh allare form C1 axiell, h oger, Skaftdiameter d1: 50mm****Best llningsdata**

Ordernummer	319107 50
GTIN	4067263224488
Artikelklass	32V

**Beskrivning****Utf rande:**

- S tth rdad HRC 58  $\pm$ 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

**Anv ndningsdata:**

F r  ndbearbetning.

**Norm:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Teknisk beskrivning**

$h_2$	34 mm
$b_2$	50 mm
Skaftbredd $b_3$	26 mm
$h_5$	50 mm
$l_1$	100 mm
$h_6$	60 mm
F�rgkod VDI-skaft	VDI 50

b <sub>1</sub>	100 mm
h <sub>1</sub>	32 mm
Skaftdiameter d <sub>1</sub>	50 mm
Form	C
Produktslag	VDi-verktygshållare