

**Verkt ygsh allare form C1 axiell, h oger, Skaftdiameter d1: 30mm****Best llningsdata**

Ordernummer	319107 30
GTIN	4067263224464
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rdad HRC 58 \pm 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Teknisk beskrivning

h_1	20 mm
b_1	70 mm
h_6	38 mm
h_2	29 mm
b_2	35 mm
l_1	70 mm
F�rgkod VDI-skaft	VDI 30

Skaftbredd b_3	17 mm
h_5	28 mm
Skaftdiameter d_1	30 mm
Form	C
Produktslag	VDi-verktygshållare