

**Verkt ygsh allare form C2 axiell, v nster, Skaftdiameter d1: 16mm****Best llningsdata**

Ordernummer	319117 16
GTIN	4067263224495
Artikelklass	32V

**Beskrivning****Utf rande:**

- S tth rddad HRC 58  $\pm$ 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

**Anv ndningsdata:**

F r  ndbearbetning.

**Norm:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Teknisk beskrivning**

F�rgkod VDI-skaft	VDI 16
Skaftbredd b <sub>3</sub>	13 mm
Skaftdiameter d <sub>1</sub>	16 mm
h <sub>2</sub>	17 mm
h <sub>5</sub>	20 mm
h <sub>6</sub>	22 mm
b <sub>1</sub>	43 mm

b <sub>2</sub>	24 mm
h <sub>1</sub>	12 mm
l <sub>1</sub>	44 mm
Form	C
Produktslag	VDi-verktygshållare