

**Verkt ygsh allare form C3 axiell, h oger, Skaftdiameter d1: 16mm****Best llningsdata**

Ordernummer	319127 16
GTIN	4067263237457
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rddad HRC 58 \pm 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Teknisk beskrivning

b ₂	24 mm
h ₁	12 mm
h ₅	20 mm
Skaftdiameter d ₁	16 mm
b ₁	43 mm
Skaftbredd b ₃	13 mm
h ₆	22 mm

Färgkod VDI-skaft	VDI 16
l_1	44 mm
h_2	17 mm
Form	C
Produktslag	VDi-verktygshållare