

**Verkt ygsh allare form C4 axiell, v nster, Skaftdiameter d1: 40mm****Best llningsdata**

Ordernummer	319137 40
GTIN	4067263237631
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rdad HRC 58 \pm 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Teknisk beskrivning

F�rgkod VDI-skaft	VDI 40
l_1	85 mm
b_1	85 mm
b_2	42,5 mm
Skaftdiameter d_1	40 mm
h_6	48 mm
h_5	32,5 mm

h ₁	25 mm
h ₂	34 mm
Skaftbredd b ₃	25,5 mm
Form	C
Produktslag	VDi-verktygshållare