

**Verkt ygsh allare form C4 axiell, v nster, Skaftdiameter d1: 16mm****Best llningsdata**

Ordernummer	319137 16
GTIN	4067263237600
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rdad HRC 58 \pm 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Teknisk beskrivning

h ₁	12 mm
Skaftdiameter d ₁	16 mm
h ₆	22 mm
h ₂	17 mm
b ₂	24 mm
F�rgkod VDI-skaft	VDI 16
h ₅	20 mm

Skaftbredd b_3	13 mm
l_1	44 mm
b_1	43 mm
Form	C
Produktslag	VDi-verktygshållare