

**Verkt ygsh allare form C1 axiell h oger, Skaftdiameter d1: 50 mm****Best llningsdata**

Ordernummer	319100 50
GTIN	4045197373724
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rddad HRC 58 ± 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Form: C

h₁: 32 mm

h₂: 41 mm

b₁: 100 mm

b₂: 50 mm

Skaftbredd b₃: 26 mm

h₅: 50 mm

Teknisk beskrivning

Skaftbredd b ₃	26 mm
l ₁	100 mm

b ₂	50 mm
b ₁	100 mm
h ₆	60 mm
h ₅	50 mm
h ₂	41 mm
h ₁	32 mm
Färgkod VDI-skaft	VDI 50
Skaftdiameter d ₁	50 mm
Form	C
Produktslag	VDi-verktygshållare

Tillbehör

Monteringsnyckel för kulmunstycke Storlek 10	319003 10
--	-----------