

**Verkt ygsh allare form C3 axiell h oger, Skaftdiameter d₁: 40 mm****Best llningsdata**

Ordernummer	319160 40
GTIN	4045197373786
Artikelklass	32V

Beskrivning**Utf rande:**

- S tth rdad HRC 58 ± 2.
- Alla funktionsytor slipade.
- Med kulventildysor.

Anv ndningsdata:

F r  ndbearbetning.

Norm:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Form: C

h₁: 25 mm

h₂: 34 mm

b₁: 85 mm

b₂: 42,5 mm

Skaftbredd b₃: 20,5 mm

h₅: 32,5 mm

Teknisk beskrivning

h ₅	32,5 mm
Skaftdiameter d ₁	40 mm
h ₆	48 mm

b_1	85 mm
Skafthbredd b_3	20,5 mm
h_1	25 mm
h_2	34 mm
l_1	85 mm
Färgkod VDI-skaft	VDI 40
b_2	42,5 mm
Form	C
Produktslag	VDi-verktygshållare