

**HOLEX**

**Garment locker with base and sloping roof attachment, for clean & dirty separation and DOM cylinder lock, Number of compartments: 4**



## Order data

Order number	949731 4
GTIN	4067263828778
Item class	92S

## Description

### Version:

Garment locker with extra wide split compartment, for clean & dirty separation. The partition within a compartment is for hygienic separation of street clothes and work clothes. The two swing doors close to each other and are centrally locked with a single lock. Doors with diamond pattern ventilation holes and label frame. With welded-in hat shelf. Hanger rail with 3 sliding clothes hooks.

With base.

With high-quality cylinder lock.

### Standard:

**DIN 4547**

### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

### Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

## Technical description

Height at the rear	2180 mm
Shelf width	298 mm
Depth	500 mm
Width	1200 mm
usable width of each compartment	2 × 240 mm
usable depth of each compartment	477 mm
usable height of each clothing compartment	1420 mm
Weight	75 kg
usable height of each hat compartment with sloping roof	328 - 530 mm
Height at the front	1950 mm
Storage shelf depth	477 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

## Accessories

Lock barrel with 2 keys Lock number Ho (3-digit) 001	950050 001
Lock barrel with 2 keys Lock number Ho (3-digit) 002	950050 002
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Lock barrel with 2 keys Lock number Ho (3-digit) 004	950050 004
Lock barrel with 2 keys Lock number Ho (3-digit) 005	950050 005
Lock barrel with 2 keys Lock number Ho (3-digit) 006	950050 006
Lock barrel with 2 keys Lock number Ho (3-digit) 007	950050 007
Lock barrel with 2 keys Lock number Ho (3-digit) 008	950050 008
Lock barrel with 2 keys Lock number Ho (3-digit) 009	950050 009

Lock barrel with 2 keys Lock number Ho (3-digit) 010	950050 010
Lock barrel with 2 keys Lock number Ho (3-digit) 011	950050 011
Lock barrel with 2 keys Lock number Ho (3-digit) 012	950050 012
Lock barrel with 2 keys Lock number Ho (3-digit) 013	950050 013
Lock barrel with 2 keys Lock number Ho (3-digit) 014	950050 014
Lock barrel with 2 keys Lock number Ho (3-digit) 015	950050 015
Lock barrel with 2 keys Lock number Ho (3-digit) 016	950050 016
Lock barrel with 2 keys Lock number Ho (3-digit) 017	950050 017
Lock barrel with 2 keys Lock number Ho (3-digit) 018	950050 018
Lock barrel with 2 keys Lock number Ho (3-digit) 019	950050 019
Lock barrel with 2 keys Lock number Ho (3-digit) 020	950050 020
Lock barrel with 2 keys Lock number Ho (3-digit) 021	950050 021
Lock barrel with 2 keys Lock number Ho (3-digit) 022	950050 022
Lock barrel with 2 keys Lock number Ho (3-digit) 023	950050 023
Lock barrel with 2 keys Lock number Ho (3-digit) 024	950050 024
Lock barrel with 2 keys Lock number Ho (3-digit) 025	950050 025
Lock barrel with 2 keys Lock number Ho (3-digit) 026	950050 026
Lock barrel with 2 keys Lock number Ho (3-digit) 027	950050 027
Lock barrel with 2 keys Lock number Ho (3-digit) 028	950050 028
Lock barrel with 2 keys Lock number Ho (3-digit) 029	950050 029
Lock barrel with 2 keys Lock number Ho (3-digit) 030	950050 030
Lock barrel with 2 keys Lock number Ho (3-digit) 031	950050 031
Lock barrel with 2 keys Lock number Ho (3-digit) 032	950050 032
Lock barrel with 2 keys Lock number Ho (3-digit) 033	950050 033
Lock barrel with 2 keys Lock number Ho (3-digit) 034	950050 034
Lock barrel with 2 keys Lock number Ho (3-digit) 035	950050 035
Lock barrel with 2 keys Lock number Ho (3-digit) 036	950050 036
Lock barrel with 2 keys Lock number Ho (3-digit) 037	950050 037
Lock barrel with 2 keys Lock number Ho (3-digit) 038	950050 038

Lock barrel with 2 keys Lock number Ho (3-digit) 039	950050 039
Lock barrel with 2 keys Lock number Ho (3-digit) 040	950050 040
Lock barrel with 2 keys Lock number Ho (3-digit) 041	950050 041
Lock barrel with 2 keys Lock number Ho (3-digit) 042	950050 042
Lock barrel with 2 keys Lock number Ho (3-digit) 043	950050 043
Lock barrel with 2 keys Lock number Ho (3-digit) 044	950050 044
Lock barrel with 2 keys Lock number Ho (3-digit) 045	950050 045
Lock barrel with 2 keys Lock number Ho (3-digit) 046	950050 046
Lock barrel with 2 keys Lock number Ho (3-digit) 047	950050 047
Lock barrel with 2 keys Lock number Ho (3-digit) 048	950050 048
Lock barrel with 2 keys Lock number Ho (3-digit) 049	950050 049
Lock barrel with 2 keys Lock number Ho (3-digit) 050	950050 050
Lock barrel with 2 keys Lock number Ho (3-digit) 051	950050 051
Lock barrel with 2 keys Lock number Ho (3-digit) 052	950050 052
Lock barrel with 2 keys Lock number Ho (3-digit) 053	950050 053
Lock barrel with 2 keys Lock number Ho (3-digit) 054	950050 054
Lock barrel with 2 keys Lock number Ho (3-digit) 055	950050 055
Lock barrel with 2 keys Lock number Ho (3-digit) 056	950050 056
Lock barrel with 2 keys Lock number Ho (3-digit) 057	950050 057
Lock barrel with 2 keys Lock number Ho (3-digit) 058	950050 058
Lock barrel with 2 keys Lock number Ho (3-digit) 059	950050 059
Lock barrel with 2 keys Lock number Ho (3-digit) 060	950050 060
Lock barrel with 2 keys Lock number Ho (3-digit) 061	950050 061
Lock barrel with 2 keys Lock number Ho (3-digit) 062	950050 062
Lock barrel with 2 keys Lock number Ho (3-digit) 063	950050 063
Lock barrel with 2 keys Lock number Ho (3-digit) 064	950050 064
Lock barrel with 2 keys Lock number Ho (3-digit) 065	950050 065
Lock barrel with 2 keys Lock number Ho (3-digit) 066	950050 066
Lock barrel with 2 keys Lock number Ho (3-digit) 067	950050 067

Lock barrel with 2 keys Lock number Ho (3-digit) 068	950050 068
Lock barrel with 2 keys Lock number Ho (3-digit) 069	950050 069
Lock barrel with 2 keys Lock number Ho (3-digit) 070	950050 070
Lock barrel with 2 keys Lock number Ho (3-digit) 071	950050 071
Lock barrel with 2 keys Lock number Ho (3-digit) 072	950050 072
Lock barrel with 2 keys Lock number Ho (3-digit) 073	950050 073
Lock barrel with 2 keys Lock number Ho (3-digit) 074	950050 074
Lock barrel with 2 keys Lock number Ho (3-digit) 075	950050 075
Lock barrel with 2 keys Lock number Ho (3-digit) 076	950050 076
Lock barrel with 2 keys Lock number Ho (3-digit) 077	950050 077
Lock barrel with 2 keys Lock number Ho (3-digit) 078	950050 078
Lock barrel with 2 keys Lock number Ho (3-digit) 079	950050 079
Lock barrel with 2 keys Lock number Ho (3-digit) 080	950050 080
Lock barrel with 2 keys Lock number Ho (3-digit) 081	950050 081
Lock barrel with 2 keys Lock number Ho (3-digit) 082	950050 082
Lock barrel with 2 keys Lock number Ho (3-digit) 083	950050 083
Lock barrel with 2 keys Lock number Ho (3-digit) 084	950050 084
Lock barrel with 2 keys Lock number Ho (3-digit) 085	950050 085
Lock barrel with 2 keys Lock number Ho (3-digit) 086	950050 086
Lock barrel with 2 keys Lock number Ho (3-digit) 087	950050 087
Lock barrel with 2 keys Lock number Ho (3-digit) 088	950050 088
Lock barrel with 2 keys Lock number Ho (3-digit) 089	950050 089
Lock barrel with 2 keys Lock number Ho (3-digit) 090	950050 090
Lock barrel with 2 keys Lock number Ho (3-digit) 091	950050 091
Lock barrel with 2 keys Lock number Ho (3-digit) 092	950050 092
Lock barrel with 2 keys Lock number Ho (3-digit) 093	950050 093
Lock barrel with 2 keys Lock number Ho (3-digit) 094	950050 094
Lock barrel with 2 keys Lock number Ho (3-digit) 095	950050 095
Lock barrel with 2 keys Lock number Ho (3-digit) 096	950050 096

Lock barrel with 2 keys Lock number Ho (3-digit) 097	950050 097
Lock barrel with 2 keys Lock number Ho (3-digit) 098	950050 098
Lock barrel with 2 keys Lock number Ho (3-digit) 099	950050 099
Lock barrel with 2 keys Lock number Ho (3-digit) 100	950050 100
Lock barrel with 2 keys Lock number Ho (3-digit) 101	950050 101
Lock barrel with 2 keys Lock number Ho (3-digit) 102	950050 102
Lock barrel with 2 keys Lock number Ho (3-digit) 103	950050 103
Lock barrel with 2 keys Lock number Ho (3-digit) 104	950050 104
Lock barrel with 2 keys Lock number Ho (3-digit) 105	950050 105
Lock barrel with 2 keys Lock number Ho (3-digit) 106	950050 106
Lock barrel with 2 keys Lock number Ho (3-digit) 107	950050 107
Lock barrel with 2 keys Lock number Ho (3-digit) 108	950050 108
Lock barrel with 2 keys Lock number Ho (3-digit) 109	950050 109
Lock barrel with 2 keys Lock number Ho (3-digit) 110	950050 110
Lock barrel with 2 keys Lock number Ho (3-digit) 111	950050 111
Lock barrel with 2 keys Lock number Ho (3-digit) 112	950050 112
Lock barrel with 2 keys Lock number Ho (3-digit) 113	950050 113
Lock barrel with 2 keys Lock number Ho (3-digit) 114	950050 114
Lock barrel with 2 keys Lock number Ho (3-digit) 115	950050 115
Lock barrel with 2 keys Lock number Ho (3-digit) 116	950050 116
Lock barrel with 2 keys Lock number Ho (3-digit) 117	950050 117
Lock barrel with 2 keys Lock number Ho (3-digit) 118	950050 118
Lock barrel with 2 keys Lock number Ho (3-digit) 119	950050 119
Lock barrel with 2 keys Lock number Ho (3-digit) 120	950050 120
Lock barrel with 2 keys Lock number Ho (3-digit) 121	950050 121
Lock barrel with 2 keys Lock number Ho (3-digit) 122	950050 122
Lock barrel with 2 keys Lock number Ho (3-digit) 123	950050 123
Lock barrel with 2 keys Lock number Ho (3-digit) 124	950050 124
Lock barrel with 2 keys Lock number Ho (3-digit) 125	950050 125

Lock barrel with 2 keys Lock number Ho (3-digit) 126	950050 126
Lock barrel with 2 keys Lock number Ho (3-digit) 127	950050 127
Lock barrel with 2 keys Lock number Ho (3-digit) 128	950050 128
Lock barrel with 2 keys Lock number Ho (3-digit) 129	950050 129
Lock barrel with 2 keys Lock number Ho (3-digit) 130	950050 130
Lock barrel with 2 keys Lock number Ho (3-digit) 131	950050 131
Lock barrel with 2 keys Lock number Ho (3-digit) 132	950050 132
Lock barrel with 2 keys Lock number Ho (3-digit) 133	950050 133
Lock barrel with 2 keys Lock number Ho (3-digit) 134	950050 134
Lock barrel with 2 keys Lock number Ho (3-digit) 135	950050 135
Lock barrel with 2 keys Lock number Ho (3-digit) 136	950050 136
Lock barrel with 2 keys Lock number Ho (3-digit) 137	950050 137
Lock barrel with 2 keys Lock number Ho (3-digit) 138	950050 138
Lock barrel with 2 keys Lock number Ho (3-digit) 139	950050 139
Lock barrel with 2 keys Lock number Ho (3-digit) 140	950050 140
Lock barrel with 2 keys Lock number Ho (3-digit) 141	950050 141
Lock barrel with 2 keys Lock number Ho (3-digit) 142	950050 142
Lock barrel with 2 keys Lock number Ho (3-digit) 143	950050 143
Lock barrel with 2 keys Lock number Ho (3-digit) 144	950050 144
Lock barrel with 2 keys Lock number Ho (3-digit) 145	950050 145
Lock barrel with 2 keys Lock number Ho (3-digit) 146	950050 146
Lock barrel with 2 keys Lock number Ho (3-digit) 147	950050 147
Lock barrel with 2 keys Lock number Ho (3-digit) 148	950050 148
Lock barrel with 2 keys Lock number Ho (3-digit) 149	950050 149
Lock barrel with 2 keys Lock number Ho (3-digit) 150	950050 150
Lock barrel with 2 keys Lock number Ho (3-digit) 151	950050 151
Lock barrel with 2 keys Lock number Ho (3-digit) 152	950050 152
Lock barrel with 2 keys Lock number Ho (3-digit) 153	950050 153
Lock barrel with 2 keys Lock number Ho (3-digit) 154	950050 154

Lock barrel with 2 keys Lock number Ho (3-digit) 155	950050 155
Lock barrel with 2 keys Lock number Ho (3-digit) 156	950050 156
Lock barrel with 2 keys Lock number Ho (3-digit) 157	950050 157
Lock barrel with 2 keys Lock number Ho (3-digit) 158	950050 158
Lock barrel with 2 keys Lock number Ho (3-digit) 159	950050 159
Lock barrel with 2 keys Lock number Ho (3-digit) 160	950050 160
Lock barrel with 2 keys Lock number Ho (3-digit) 161	950050 161
Lock barrel with 2 keys Lock number Ho (3-digit) 162	950050 162
Lock barrel with 2 keys Lock number Ho (3-digit) 163	950050 163
Lock barrel with 2 keys Lock number Ho (3-digit) 164	950050 164
Lock barrel with 2 keys Lock number Ho (3-digit) 165	950050 165
Lock barrel with 2 keys Lock number Ho (3-digit) 166	950050 166
Lock barrel with 2 keys Lock number Ho (3-digit) 167	950050 167
Lock barrel with 2 keys Lock number Ho (3-digit) 168	950050 168
Lock barrel with 2 keys Lock number Ho (3-digit) 169	950050 169
Lock barrel with 2 keys Lock number Ho (3-digit) 170	950050 170
Lock barrel with 2 keys Lock number Ho (3-digit) 171	950050 171
Lock barrel with 2 keys Lock number Ho (3-digit) 172	950050 172
Lock barrel with 2 keys Lock number Ho (3-digit) 173	950050 173
Lock barrel with 2 keys Lock number Ho (3-digit) 174	950050 174
Lock barrel with 2 keys Lock number Ho (3-digit) 175	950050 175
Lock barrel with 2 keys Lock number Ho (3-digit) 176	950050 176
Lock barrel with 2 keys Lock number Ho (3-digit) 177	950050 177
Lock barrel with 2 keys Lock number Ho (3-digit) 178	950050 178
Lock barrel with 2 keys Lock number Ho (3-digit) 179	950050 179
Lock barrel with 2 keys Lock number Ho (3-digit) 180	950050 180
Lock barrel with 2 keys Lock number Ho (3-digit) 181	950050 181
Lock barrel with 2 keys Lock number Ho (3-digit) 182	950050 182
Lock barrel with 2 keys Lock number Ho (3-digit) 183	950050 183



Lock barrel with 2 keys Lock number Ho (3-digit) 184	950050 184
Lock barrel with 2 keys Lock number Ho (3-digit) 185	950050 185
Lock barrel with 2 keys Lock number Ho (3-digit) 186	950050 186
Lock barrel with 2 keys Lock number Ho (3-digit) 187	950050 187
Lock barrel with 2 keys Lock number Ho (3-digit) 188	950050 188
Lock barrel with 2 keys Lock number Ho (3-digit) 189	950050 189
Lock barrel with 2 keys Lock number Ho (3-digit) 190	950050 190
Lock barrel with 2 keys Lock number Ho (3-digit) 191	950050 191
Lock barrel with 2 keys Lock number Ho (3-digit) 192	950050 192
Lock barrel with 2 keys Lock number Ho (3-digit) 193	950050 193
Lock barrel with 2 keys Lock number Ho (3-digit) 194	950050 194
Lock barrel with 2 keys Lock number Ho (3-digit) 195	950050 195
Lock barrel with 2 keys Lock number Ho (3-digit) 196	950050 196
Lock barrel with 2 keys Lock number Ho (3-digit) 197	950050 197
Lock barrel with 2 keys Lock number Ho (3-digit) 198	950050 198
Lock barrel with 2 keys Lock number Ho (3-digit) 199	950050 199
Lock barrel with 2 keys Lock number Ho (3-digit) 200	950050 200
Replacement key Lock number Ho (3-digit) 001	950060 001
Replacement key Lock number Ho (3-digit) 002	950060 002
Replacement key Lock number Ho (3-digit) 003	950060 003
Replacement key Lock number Ho (3-digit) 004	950060 004
Replacement key Lock number Ho (3-digit) 005	950060 005
Replacement key Lock number Ho (3-digit) 006	950060 006
Replacement key Lock number Ho (3-digit) 007	950060 007
Replacement key Lock number Ho (3-digit) 008	950060 008
Replacement key Lock number Ho (3-digit) 009	950060 009
Replacement key Lock number Ho (3-digit) 010	950060 010
Replacement key Lock number Ho (3-digit) 011	950060 011
Replacement key Lock number Ho (3-digit) 012	950060 012

Replacement key Lock number Ho (3-digit) 013	950060 013
Replacement key Lock number Ho (3-digit) 014	950060 014
Replacement key Lock number Ho (3-digit) 015	950060 015
Replacement key Lock number Ho (3-digit) 016	950060 016
Replacement key Lock number Ho (3-digit) 017	950060 017
Replacement key Lock number Ho (3-digit) 018	950060 018
Replacement key Lock number Ho (3-digit) 019	950060 019
Replacement key Lock number Ho (3-digit) 020	950060 020
Replacement key Lock number Ho (3-digit) 021	950060 021
Replacement key Lock number Ho (3-digit) 022	950060 022
Replacement key Lock number Ho (3-digit) 023	950060 023
Replacement key Lock number Ho (3-digit) 024	950060 024
Replacement key Lock number Ho (3-digit) 025	950060 025
Replacement key Lock number Ho (3-digit) 026	950060 026
Replacement key Lock number Ho (3-digit) 027	950060 027
Replacement key Lock number Ho (3-digit) 028	950060 028
Replacement key Lock number Ho (3-digit) 029	950060 029
Replacement key Lock number Ho (3-digit) 030	950060 030
Replacement key Lock number Ho (3-digit) 031	950060 031
Replacement key Lock number Ho (3-digit) 032	950060 032
Replacement key Lock number Ho (3-digit) 033	950060 033
Replacement key Lock number Ho (3-digit) 034	950060 034
Replacement key Lock number Ho (3-digit) 035	950060 035
Replacement key Lock number Ho (3-digit) 036	950060 036
Replacement key Lock number Ho (3-digit) 037	950060 037
Replacement key Lock number Ho (3-digit) 038	950060 038
Replacement key Lock number Ho (3-digit) 039	950060 039
Replacement key Lock number Ho (3-digit) 040	950060 040
Replacement key Lock number Ho (3-digit) 041	950060 041

Replacement key Lock number Ho (3-digit) 042	950060 042
Replacement key Lock number Ho (3-digit) 043	950060 043
Replacement key Lock number Ho (3-digit) 044	950060 044
Replacement key Lock number Ho (3-digit) 045	950060 045
Replacement key Lock number Ho (3-digit) 046	950060 046
Replacement key Lock number Ho (3-digit) 047	950060 047
Replacement key Lock number Ho (3-digit) 048	950060 048
Replacement key Lock number Ho (3-digit) 049	950060 049
Replacement key Lock number Ho (3-digit) 050	950060 050
Replacement key Lock number Ho (3-digit) 051	950060 051
Replacement key Lock number Ho (3-digit) 052	950060 052
Replacement key Lock number Ho (3-digit) 053	950060 053
Replacement key Lock number Ho (3-digit) 054	950060 054
Replacement key Lock number Ho (3-digit) 055	950060 055
Replacement key Lock number Ho (3-digit) 056	950060 056
Replacement key Lock number Ho (3-digit) 057	950060 057
Replacement key Lock number Ho (3-digit) 058	950060 058
Replacement key Lock number Ho (3-digit) 059	950060 059
Replacement key Lock number Ho (3-digit) 060	950060 060
Replacement key Lock number Ho (3-digit) 061	950060 061
Replacement key Lock number Ho (3-digit) 062	950060 062
Replacement key Lock number Ho (3-digit) 063	950060 063
Replacement key Lock number Ho (3-digit) 064	950060 064
Replacement key Lock number Ho (3-digit) 065	950060 065
Replacement key Lock number Ho (3-digit) 066	950060 066
Replacement key Lock number Ho (3-digit) 067	950060 067
Replacement key Lock number Ho (3-digit) 068	950060 068
Replacement key Lock number Ho (3-digit) 069	950060 069
Replacement key Lock number Ho (3-digit) 070	950060 070

Replacement key Lock number Ho (3-digit) 071	950060 071
Replacement key Lock number Ho (3-digit) 072	950060 072
Replacement key Lock number Ho (3-digit) 073	950060 073
Replacement key Lock number Ho (3-digit) 074	950060 074
Replacement key Lock number Ho (3-digit) 075	950060 075
Replacement key Lock number Ho (3-digit) 076	950060 076
Replacement key Lock number Ho (3-digit) 077	950060 077
Replacement key Lock number Ho (3-digit) 078	950060 078
Replacement key Lock number Ho (3-digit) 079	950060 079
Replacement key Lock number Ho (3-digit) 080	950060 080
Replacement key Lock number Ho (3-digit) 081	950060 081
Replacement key Lock number Ho (3-digit) 082	950060 082
Replacement key Lock number Ho (3-digit) 083	950060 083
Replacement key Lock number Ho (3-digit) 084	950060 084
Replacement key Lock number Ho (3-digit) 085	950060 085
Replacement key Lock number Ho (3-digit) 086	950060 086
Replacement key Lock number Ho (3-digit) 087	950060 087
Replacement key Lock number Ho (3-digit) 088	950060 088
Replacement key Lock number Ho (3-digit) 089	950060 089
Replacement key Lock number Ho (3-digit) 090	950060 090
Replacement key Lock number Ho (3-digit) 091	950060 091
Replacement key Lock number Ho (3-digit) 092	950060 092
Replacement key Lock number Ho (3-digit) 093	950060 093
Replacement key Lock number Ho (3-digit) 094	950060 094
Replacement key Lock number Ho (3-digit) 095	950060 095
Replacement key Lock number Ho (3-digit) 096	950060 096
Replacement key Lock number Ho (3-digit) 097	950060 097
Replacement key Lock number Ho (3-digit) 098	950060 098
Replacement key Lock number Ho (3-digit) 099	950060 099

Replacement key Lock number Ho (3-digit) 100	950060 100
Replacement key Lock number Ho (3-digit) 101	950060 101
Replacement key Lock number Ho (3-digit) 102	950060 102
Replacement key Lock number Ho (3-digit) 103	950060 103
Replacement key Lock number Ho (3-digit) 104	950060 104
Replacement key Lock number Ho (3-digit) 105	950060 105
Replacement key Lock number Ho (3-digit) 106	950060 106
Replacement key Lock number Ho (3-digit) 107	950060 107
Replacement key Lock number Ho (3-digit) 108	950060 108
Replacement key Lock number Ho (3-digit) 109	950060 109
Replacement key Lock number Ho (3-digit) 110	950060 110
Replacement key Lock number Ho (3-digit) 111	950060 111
Replacement key Lock number Ho (3-digit) 112	950060 112
Replacement key Lock number Ho (3-digit) 113	950060 113
Replacement key Lock number Ho (3-digit) 114	950060 114
Replacement key Lock number Ho (3-digit) 115	950060 115
Replacement key Lock number Ho (3-digit) 116	950060 116
Replacement key Lock number Ho (3-digit) 117	950060 117
Replacement key Lock number Ho (3-digit) 118	950060 118
Replacement key Lock number Ho (3-digit) 119	950060 119
Replacement key Lock number Ho (3-digit) 120	950060 120
Replacement key Lock number Ho (3-digit) 121	950060 121
Replacement key Lock number Ho (3-digit) 122	950060 122
Replacement key Lock number Ho (3-digit) 123	950060 123
Replacement key Lock number Ho (3-digit) 124	950060 124
Replacement key Lock number Ho (3-digit) 125	950060 125
Replacement key Lock number Ho (3-digit) 126	950060 126
Replacement key Lock number Ho (3-digit) 127	950060 127
Replacement key Lock number Ho (3-digit) 128	950060 128

Replacement key Lock number Ho (3-digit) 129	950060 129
Replacement key Lock number Ho (3-digit) 130	950060 130
Replacement key Lock number Ho (3-digit) 131	950060 131
Replacement key Lock number Ho (3-digit) 132	950060 132
Replacement key Lock number Ho (3-digit) 133	950060 133
Replacement key Lock number Ho (3-digit) 134	950060 134
Replacement key Lock number Ho (3-digit) 135	950060 135
Replacement key Lock number Ho (3-digit) 136	950060 136
Replacement key Lock number Ho (3-digit) 137	950060 137
Replacement key Lock number Ho (3-digit) 138	950060 138
Replacement key Lock number Ho (3-digit) 139	950060 139
Replacement key Lock number Ho (3-digit) 140	950060 140
Replacement key Lock number Ho (3-digit) 141	950060 141
Replacement key Lock number Ho (3-digit) 142	950060 142
Replacement key Lock number Ho (3-digit) 143	950060 143
Replacement key Lock number Ho (3-digit) 144	950060 144
Replacement key Lock number Ho (3-digit) 145	950060 145
Replacement key Lock number Ho (3-digit) 146	950060 146
Replacement key Lock number Ho (3-digit) 147	950060 147
Replacement key Lock number Ho (3-digit) 148	950060 148
Replacement key Lock number Ho (3-digit) 149	950060 149
Replacement key Lock number Ho (3-digit) 150	950060 150
Replacement key Lock number Ho (3-digit) 151	950060 151
Replacement key Lock number Ho (3-digit) 152	950060 152
Replacement key Lock number Ho (3-digit) 153	950060 153
Replacement key Lock number Ho (3-digit) 154	950060 154
Replacement key Lock number Ho (3-digit) 155	950060 155
Replacement key Lock number Ho (3-digit) 156	950060 156
Replacement key Lock number Ho (3-digit) 157	950060 157

Replacement key Lock number Ho (3-digit) 158	950060 158
Replacement key Lock number Ho (3-digit) 159	950060 159
Replacement key Lock number Ho (3-digit) 160	950060 160
Replacement key Lock number Ho (3-digit) 161	950060 161
Replacement key Lock number Ho (3-digit) 162	950060 162
Replacement key Lock number Ho (3-digit) 163	950060 163
Replacement key Lock number Ho (3-digit) 164	950060 164
Replacement key Lock number Ho (3-digit) 165	950060 165
Replacement key Lock number Ho (3-digit) 166	950060 166
Replacement key Lock number Ho (3-digit) 167	950060 167
Replacement key Lock number Ho (3-digit) 168	950060 168
Replacement key Lock number Ho (3-digit) 169	950060 169
Replacement key Lock number Ho (3-digit) 170	950060 170
Replacement key Lock number Ho (3-digit) 171	950060 171
Replacement key Lock number Ho (3-digit) 172	950060 172
Replacement key Lock number Ho (3-digit) 173	950060 173
Replacement key Lock number Ho (3-digit) 174	950060 174
Replacement key Lock number Ho (3-digit) 175	950060 175
Replacement key Lock number Ho (3-digit) 176	950060 176
Replacement key Lock number Ho (3-digit) 177	950060 177
Replacement key Lock number Ho (3-digit) 178	950060 178
Replacement key Lock number Ho (3-digit) 179	950060 179
Replacement key Lock number Ho (3-digit) 180	950060 180
Replacement key Lock number Ho (3-digit) 181	950060 181
Replacement key Lock number Ho (3-digit) 182	950060 182
Replacement key Lock number Ho (3-digit) 183	950060 183
Replacement key Lock number Ho (3-digit) 184	950060 184
Replacement key Lock number Ho (3-digit) 185	950060 185
Replacement key Lock number Ho (3-digit) 186	950060 186

Replacement key Lock number Ho (3-digit) 187	950060 187
Replacement key Lock number Ho (3-digit) 188	950060 188
Replacement key Lock number Ho (3-digit) 189	950060 189
Replacement key Lock number Ho (3-digit) 190	950060 190
Replacement key Lock number Ho (3-digit) 191	950060 191
Replacement key Lock number Ho (3-digit) 192	950060 192
Replacement key Lock number Ho (3-digit) 193	950060 193
Replacement key Lock number Ho (3-digit) 194	950060 194
Replacement key Lock number Ho (3-digit) 195	950060 195
Replacement key Lock number Ho (3-digit) 196	950060 196
Replacement key Lock number Ho (3-digit) 197	950060 197
Replacement key Lock number Ho (3-digit) 198	950060 198
Replacement key Lock number Ho (3-digit) 199	950060 199
Replacement key Lock number Ho (3-digit) 200	950060 200