SWISSTOOLS

Boring bar shank, HSK-T, Shank ∅ / ∅ D - A dimension: 63/40-140mm

Order data

Order number	320102 63/40-140
GTIN	2050001772930
Item class	36D

Description

Version:
· **For efficient turning.**
· **For left-hand and right-hand turning.**
Application:
For mounting exchangeable cutting heads.
Note:
For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Overhang dimension A	140 mm
Shank ∅	63 mm
∅ D	40 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body