ata tools

Pneumatic straight die grinder, Type: SMP60

Order data

Order number	079440 SMP60
GTIN	5000630
Item class	03P

Description

Version:
ATA – Pneumatic straight die grinder **with 3 mm collets** for fine milling, grinding and engraving. **Integral pre-filter.** Turbine-driven small straight die grinder with a **maximum speed of 60,000 rpm.**

Technical description

Output power	85 W
Collet ∅	3 mm
Operating noise	68 dB(A)
Manufacturer's designation	SPM 60 R
Weight	0.17 kg
maximum air consumption	230 l/min
maximum speed	60000 min^{-1}
maximum vibration to EN	< 2.5 m/s^2
Length	140 mm
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Straight die grinder