Garant GRIDLINE

Hexagonal workbench, 20×20G, Model: T3

Order data

Order number	925814 T3
GTIN	4062406102159
Item class	9GG

Description

Version:
Hexagonal workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.
50 mm thick worktop made of beech marine ply. Finished with clear UV varnish.
Fitted with:
Drawer front heights, mm: 75, 75, 100
Door heights, mm: 425
Supplied with:
6 drawer casings, 6 intermediate panels, worktop, fastenings.
Colour:
Casing body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**
Note:
Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer body height	800 mm
Drawer body width	600 mm
Drawer usable width	500 mm
Drawer body depth	650 mm

Material of worktop	Beech marine ply
Surface worktop	clear varnished
Drawer usable depth	500 mm
Weight	462 kg
Height	850 mm
Number of drawers	3
ComfortClose	no
Series	vario
Drawer usable area in G	20×20
Drawer usable depth in G	20
Drawer usable width in G	20
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	2000 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Hexagonal workbench

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927800 75

Drawer Drawer front height 100 mm	927800 100
Lock plate for GridLine Type KO21	914227 KO21