Garant

Grooving toolholder, left-hand, Shank / groove width w: 25/1,5mm

Order data

Order number	273751 25/1,5
GTIN	4045197720078
Item class	21W

Description

Version:
Made of high-tensile tool steel (> 1300 N/mm^2). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.

Technical description

Functional width L_4	26.5 mm
Groove width w	1.5 mm
Grooving depth t_{max}	4.5 mm
Head length L_1	29 mm
Screw	279815 6 (TX25; 6 Nm)
Overall length L	150 mm
Shank width b	25 mm
Application type	left-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Boring bar

Accessories

Clamping screw Type 6	279815 6
8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25