Garant GRIDLINE

Vario workbench 5S, drawer casing 24G, height 950 mm, Beech marine ply worktop, 20×20G, Worktop length: 1500mm

Order data

Order number	922874 1500
GTIN	4062406118549
Item class	9GG

Description

Version:
Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.
Fitted with:
Drawer front height, mm: 75, 100, 100, 125, 150, 250
Supplied with:
1 × support leg, 1 × pair of stabilising plates, drawer casing, worktop.
Optional extras:
Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.
Colour:
Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Not configurable.**
Note:
Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable depth	500 mm
Drawer body depth	650 mm
Drawer body width	600 mm
Drawer usable width	500 mm
Worktop thickness	50 mm
Weight	133 kg
Number of drawers	6
Worktop length	1500 mm
Height	950 mm
Worktop depth	750 mm
Series	vario
Drawer usable depth in G	20
Drawer usable width in G	20
Drawer usable area in G	20×20
Drawer body usable height	800 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 125 mm	927800 125
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 250 mm	927800 250
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 100 mm	927800 100
Worktop thickness 50 mmof beech marine ply Worktop length 1500 mm	926081 1500
Drawer casing 24G with drawers Height / number of drawers 900/6	927600 900/6
Stabilising plate Type 1	927122 1
Support leg Height 900 mm	927000 900