HOLEX

Instant adhesive, 20 g, Type: UNI

Order data

Order number	083361 UNI
GTIN	4062406120313
Item class	02A

Description

Version:
Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity. For general purpose use, suitable for most **plastics, metal and wood.**
Note:
Not available in all countries. Express delivery not available.

Technical description

Touch dry after	5 - 40 s
Tensile shear strength	10 - 20 N/mm^2
Labelling of hazardous substances	GHS07: Exclamation mark
Dynamic viscosity	95 - 200 mPas
Storage temperature	20 °C
Chemical basis	Ethyl cyanoacrylate

Functional strength to	10 - 30 min
Suitable for material	Plastic
Suitable for material	Metal
Suitable for material	wood
Shape	liquid
Tensile strength	10 - 20 N/mm^2
Density	1.06 g/cm^3
Operating temperature range	-55 °C
Working life after date of manufacture	9 mo
Colour	transparent
Capacity	20 ml
Product name attribute	20 g
Type of product	Instant adhesive