BOSCH

LED cordless lamp, 12 V, Type: GLI12330

Order data

Order number	073203 GLI12330
GTIN	3165140741750
Item class	03B

Description

Version:
12 V work light with 10 LEDs and two brightness levels. Adjustable angle up to 200°, suspension hook, carabiner and integral magnet.
Supplied with:
Cordless lamp without battery and without charger.
Note:
Suitable spare batteries and chargers can be found under No. 073851– 073866.

Technical description

Battery voltage	12 V
Manufacturer's designation	GLI 12-330
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	300 g
Power supply	Rechargeable battery-powered

Illumination	330 lm
Pivot range	0 - 200 degrees
ATEX zone	no
Product name attribute	12 V
suitable battery - supplier / battery type / voltage	Bosch 12 V
Type of product	Work lamp

Accessories

Li-ion battery Battery type, battery voltage B12 V	073851 B12
Li-ion battery Battery type, battery voltage B12 V	073855 B12