Garant

Torque screwdriver, fixed setting, set torque: 3,5N·m

Order data

Order number	211750 3,5
GTIN	4045197764294
Item class	21B

Description

Version:
Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.
Function:
When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.
Application:
In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank,** e.g. **Torx Plus® bit** No. **674252.** Ideal for precise tightening of indexable inserts to the specified torque.
Standard:
Geprüft nach DIN EN ISO 6789.
Note:
Supplied **without** bit.
The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Torque measuring accuracy	±10 %
Blade length	50 mm
set torque	3.5 Nm
Bit socket	D 6,3
Bit socket	F 6.3
Connection format	Bit holder 1/4 inch
Measurement process	Torque
Adjustable trigger value	non-adjustable
Trigger principle	Mechanical long travel release
Reversible reading	Nm
Standard	DIN EN ISO 6789
Overall length L	107 mm
Feedback	triggering
Setting the trigger value	preset
Direction of tightening	Right-hand tightening
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20

Accessories

“TQ-Station” – storage station for torque screwdrivers	659964