LESSMANN®
THE GERMAN BRUSH COMPANY

Wheel brush with shank Stainless steel wire 0.20 mm, Brush ∅ D1× bristle width L1: 30X6mm

Order data

Order number	574250 30X6
GTIN	4017359007075
Item class	57L

Description

Version:
Waved special high quality wire, **shank ∅ 6 mm.**
Application:
For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.
For removal of rust and scale, and for cleaning

Technical description

Bristle thickness	0.2 mm
Length of brush section H_1	6 mm
Brush ∅ D_1	30 mm
maximum speed	20000 min^{-1}
Bristle width L_1	6 mm
Shank ∅ D_s	6 mm
Brush material	Stainless steel wire

Twisted knotting	waved
Type of product	Wheel brush