JEPSON POWER

Drytec® carbide circular saw blade ∅ 355×25.4 mm for thin-walled material, Number of teeth: 90

Order data

Order number	078237 90
GTIN	4260052460146
Item class	07E

Description

Version:
Carbide-tipped circular saw blade for precise cutting.
- **Safety at work: Thin-walled, low-vibration, reduced noise.**
- **Extremely long working life.**
- **High-quality cutting.**
- **Can be resharpened 5×.**
- **General-purpose use for steel, plastic, and non-ferrous metals (not No. 078236).**

Note:
Other special saw blades for aluminium, stainless steel, for example, are available on request.

Technical description

No. of teeth optimised for	Material thickness up to 2.5 mm
Bore ∅	25.4 mm
Number of teeth	90
Blade ∅ D	355 mm

Width of cut B	2.2 mm
Tool material	Carbide
suitable for	078231 size 9435
Suitable for material	for thin-walled material
Type of product	Circular saw blade