HOLEX

Abrasive flap disc speed ZA, flat, ⌀ 125 mm, Grit: 40

Order data

Order number	GG5295 40
GTIN	4062406201746
Item class	GGN

Description

Version:
· **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
· **Glass fibre pad for optimum contact pressure.**
· **Suitable for both steel and stainless steel.**
· **Best results on angle grinders of all power classes.**
speed - flat flap strip arrangement, for **high metal removal rate** and long tool life.
Corresponds to 565295
Application:
Precise chamfering, edge smoothing and surface abrasion.
Note:
Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Bore ⌀	22.23 mm
Disc ⌀	125 mm

Shape description	flat
Contents	100
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	∅ 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm²	suitable		
Steel < 1400 N/mm²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Abrasive flap discspeed ZA, flat Grit 40	565295 40