Garant GRIDLINE

Workbench, left side open, right side 3 drawers, Beech marine ply worktop, 20×20G, Worktop length: 1500mm

Order data

Order number	920814 1500
GTIN	4062406262136
Item class	9GG

Description

Version:
Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.
Recessed open housing for ergonomic posture.
Drawer bodies always RAL 7035 light grey, **powder coated.** Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.
Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.
Fitted with:
Drawer front height (right) mm: 125, 200, 300
Optional extras:
Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.
Colour:
Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite grey, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	129 kg
Drawer usable width	500 mm
Drawer usable width in G	20
Drawer usable area in G	20×20
Worktop length	1500 mm
Worktop depth	750 mm
Support cabinet depth	700 mm
Worktop thickness	50 mm
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer body usable height	625 mm
Drawer usable depth in G	20
Support cabinet width	1300 mm
Height	950 mm
Drawer usable depth	500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Mat for drawers Dimension in G 20X20	951830 20X20
Marking out and sawing Number of tools 8	954895 8
Screwdriver set Number of tools 10	953521 10
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Drawer Drawer front height 300 mm	927800 300
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Combination spanner set Number of tools 20	952505 20
Drawer Drawer front height 200 mm	927800 200
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
File set Number of tools 6	952253 6
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Drawer Drawer front height 125 mm	927800 125
Slotted dividers / plain dividers set Drawer front height / type 125/4	950320 125/4
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Pliers set Number of tools 5	954295 5
Disassembly tool Type 1	950070 1
Lock plate for GridLine Type KO21	914227 KO21
Pliers set Number of tools 5	954305 5
Screwdriver set Number of tools 10	953522 10
Pliers set Number of tools 5	954306 5