Garant GRIDLINE

Roller cabinet with drawers 75 kg, 20×24G, Height mm / number of drawers: 885/4

Order data

Order number	931025 885/4
GTIN	4062406352561
Item class	9GK

Description

Version:
Complete with drawers 20×24G.
Roller cabinet in 24×28G with 2 each ball-bearing fixed wheels and castors, ∅ 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.
100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).
With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.
Fitted with:
Drawer front height, mm: 75, 100, 125, 300
Colour:
Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable depth	600 mm
Number of drawers	4
Drawer usable width in G	20
Number of castors with parking brake	2
ComfortClose	no
Wheel ∅	125 mm
Drawer runner extension (partial/full extension)	100 %
Usable height	600 mm
Drawer usable area in G	20×24
Number of doors	0
Drawer usable width	500 mm
with anti-roll lip	yes
maximum load capacity	600 kg
Weight	98 kg
Width	600 mm
Electronic locking system can be retrofitted	yes
Drawer usable depth in G	24
Depth	700 mm
Treadless tyres	yes
Number of fixed wheels without parking brake	2
Drawer body usable height	600 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer body height	700 mm
Height	885 mm
Individual drawer release system	One-hand
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Casing open at the top	no

Usable height for drawers	600 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×24G
Type of product	Assembly trolley

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Roller cabinet for drawers Height mm / number of drawers 885/0	931027 885/0
Drawer with one-handed individual drawer release system,75 kg Drawer front height 100 mm	931046 100
Drawer with one-handed individual drawer release system,75 kg Drawer front height 125 mm	931046 125
Drawer with one-handed individual drawer release system,75 kg Drawer front height 300 mm	931046 300
Drawer with one-handed individual drawer release system,75 kg Drawer front height 75 mm	931046 75
Drawer runners(Pair) Load capacity 75 kg	939901 75
Sheet metal cover top with raised edge on 4 sides Dimension in G 24X28	951972 24X28