Garant GRIDLINE

Roller cabinet for drawers, 36×20G, Height mm / number of drawers: 885/0

Order data

Order number	930727 885/0
GTIN	4062406352554
Item class	9GK

Description

NOTE: Colour selection possible
Version:
To take drawers 36×20G.
Roller cabinet in 40×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.
Colour:
Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**
Note:
Only No. 930744 or No. 930746 can be fitted with drawers (with one-hand individual drawer release system).
Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Height: 885 mm
Width: 1000 mm
Depth: 600 mm
Usable height: 600 mm
Drawer body height: 700 mm
Drawer body usable height: 600 mm

Technical description

Treadless tyres	yes
Usable height	600 mm
Drawer body usable height	600 mm
Weight	65 kg
Drawer body height	700 mm
maximum load capacity	600 kg
Height	885 mm
ComfortClose	no
Depth	600 mm
with anti-roll lip	yes
Wheel ∅	125 mm
Number of castors with parking brake	2
Number of doors	0
Width	1000 mm
Number of fixed wheels without parking brake	2
Electronic locking system can be retrofitted	yes
Number of drawers	0
Version	wheeled
Version	for individual configuration
Usable height for drawers	600 mm
Number of pull-out shelves	0
Casing open at the top	no
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×20G

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Sheet metal cover top with anti-roll lip on 4 sides Dimension in G 40X24	951972 40X24