Cordless impact wrench / driver, Type: 71150864

Order data

Order number	074000 71150864
GTIN	4014586891651
Item class	03F

Description

Version:
Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps.**
Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.
· **3/4-inch square drive socket.**
· **1,050 Nm max. torque.**
· **with MultiVolt interface.**
Supplied with:
Version without battery and without charger, including L-BOXX. **Without battery and without charger,** with carrying case.
Note:
See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

Tool arbor drive profile	External square drive
Number of rechargeable batteries contained	0
maximum torque	1050 Nm

Type of rechargeable battery	Lithium-ion
maximum screw ∅ (8.8 - 12.9)	M27
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Number of impacts	0 - 2200 min^{-1}
Battery voltage	12 V
Battery voltage	18 V
typical application	Heavy Duty
Manufacturer's designation	ASCD 18-1000
Tool arbor size	3/4 in
maximum vibration to EN	12.9 m/s^2
Weight	3 kg
Power supply	Rechargeable battery-powered
Type of product	Impact wrench

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE12 V	073835 FE12
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery Rechargeable battery type, battery voltage FE12 V	073837 FE12