Atlas Copco

Pneumatic straight die grinder collet ∅ 6 mm, Type: G2422

Order data

Order number	079452 G2422
GTIN	7322590011086
Item class	03R

Description

Version:
Pneumatic straight die grinder. Sturdy and smooth-running. The safety switch prevents accidental switching on.
Collet ∅ 6 mm. Long version with slim shank, ideal for holes, maximum speed **20,000 rpm.**
Supplied with:
Including the necessary coupling adaptors.
Spare part:
Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum speed	20000 min^{-1}
maximum air consumption	618 l/min
Weight	0.7 kg
Manufacturer's designation	G2422-1
Length	277 mm
maximum vibration to EN	3.4 m/s^2
Output power	350 W

Operating noise	77 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Power supply	Pneumatic
Type of product	Straight die grinder

Accessories

Collet for straight die grinder Collet ∅ 6 mm	079459 6