Pneumatic die grinder, Type: 52855

Order data

Order number	079441 52855
GTIN	616026528550
Item class	03R

Description

Version:
Dynabrade – pneumatic straight die grinder.
Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip. Adjustable straight pencil grinder. Robust pneumatic motor suitable for oiled compressed air, stepless speed regulation from 35,000 rpm – 60,000 rpm. Integrated on/off switch, memory function.
Supplied with:
Including the necessary coupling adaptors.

Technical description

Collet ∅	3 mm
maximum speed	60000 min^{-1}
Weight	0.61 kg
maximum vibration to EN	< 2.5 m/s^2
Output power	75 W
Operating noise	67 dB(A)
Length	114 mm
maximum air consumption	170 l/min

Manufacturer's designation	52855
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Straight die grinder