Atlas Copco

Pneumatic chisel hammer, Type: P2531-H

Order data

Order number	079730 P2531-H
GTIN	7322590059514
Item class	03R

Description

Version:
Handy **chisel hammer** for chiselling and separating.
Supplied with:
Including the necessary coupling adaptors.
Spare part:
Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

recommended hose size (internal ∅)	10 mm
Tool arbor size	10.2 mm
Length	193 mm
Weight	1.5 kg
maximum vibration to EN	11.5 m/s^2
maximum air consumption	402 l/min

Manufacturer's designation	P2531-H
Tool arbor shape	Hexagon
Impact frequency	50 Hz
Operating noise	100 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Power supply	Pneumatic
Type of product	Chisel mallet

Accessories

Chisel Dimensions 20X178 mm	079739 20X178
Chisel Dimensions 3,2X178 mm	079739 3,2X178