HOLEX

Lever lock toolholder set, left-hand, Shank size: 20mm

Order data

Order number	255121 20
GTIN	4062406384623
Item class	29W

Technical description

Shank size	20 mm
Functional width L_4	25 mm
ISO code toolholder	PCLNL 2020K12; PDJNL 2020K11;
suitable indexable insert	CN.. 1204..; DN.. 1104..
Spare part	259981 8
Head length L_1	28 mm
Overall length L	125 mm
Standard	DIN ISO 5610
Standard	Works standard
Application type	left-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar

Accessories

Spare parts set for lever lock toolholder Type 9	259981 9