Flat magnet with internal thread, Ferrite, ∅: 13mm

Order data

Order number	085915 13
GTIN	2050000964992
Item class	08Q

Description

Version:
· **Shielded flat magnet made of hard ferrite with insert nut.**
· **Galvanised surface.**
· **Temperature-resistant up to maximum 120 °C.**
Application:
For clamping, assembling, incorporation by screw fastening.
Note:
Screw-in hooks with external thread under No. 085921.

Technical description

∅	13 mm
Material of the surface	galvanised
Height	4.5 mm
Nominal clamping force	10 N
Threaded socket	yes
Thread	M3 mm
Height with thread	11.5 mm
Weight	5 g
maximum temperature resistance	120 °C

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread10 pieces Thread M3	085921 M3