Flat magnet with internal thread, Ferrite, ∅: 100mm

Order data

Order number	085915 100
GTIN	2050001735751
Item class	08Q

Description

Version:
· **Shielded flat magnet made of hard ferrite with insert nut.**
· **Galvanised surface.**
· **Temperature-resistant up to maximum 120 °C.**
Application:
For clamping, assembling, incorporation by screw fastening.
Note:
Screw-in hooks with external thread under No. 085921.

Technical description

∅	100 mm
Weight	940 g
Thread	M12 mm
Nominal clamping force	900 N
Height	22 mm
maximum temperature resistance	120 °C
Threaded socket	yes
Height with thread	42 mm
Material of the surface	galvanised

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet