Screw-on toolholder, left-hand, Shank / insert size: 20/07mm

Order data

Order number	260309 20/07
GTIN	4062406602260
Item class	21T

Technical description

Pack of insert screws	269028 22
Head length L_1	24 mm
Shank size	20 mm
Insert size	7 mm
Functional width L_4	24 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDJCR/L 2020K11
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500