Garant

GARANT Master Eco lever lock toolholder short, right-hand, Shank / insert size: 20/16mm

Order data

Order number	251404 20/16
GTIN	4062406734183
Item class	21U

Description

Version:
Highly efficient cooling directly on the cutter and additional flank face cooling.
Note:
Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Clamping claw	259038 20
Shim	259033 9
Shank size	20 mm
ISO code toolholder	MTJNR/L 2020X16
Series	Master Eco
suitable indexable insert	TN.. 1604..
Screw for clamping claw	259021 6
Overall length L	95 mm
Functional width L_4	25 mm

Head length L_1	35 mm
Pin	259049 8
Insert size	16 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3