Screw-on toolholder, left-hand, Shank / insert size: 10/07mm

Order data

Order number	260307 10/07
GTIN	4045197654885
Item class	21T

Technical description

Pack of insert screws	269028 22
suitable indexable insert	DC.. 0702..
Shank size	10 mm
Functional width L_4	12 mm
Head length L_1	7 mm
Insert size	7 mm
ISO code toolholder	SDHCR/L 1010E07
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500