Clamping toolholder, left-hand, Shank / insert size: 32/22mm

Order data

Order number	251407 32/22
GTIN	4045197656926
Item class	21T

Technical description

Screw set	259023 2
Insert size	22 mm
Head length L_1	36 mm
Functional width L_4	40 mm
Shim	259031 33
ISO code toolholder	MTJNR/L 3232P22
suitable indexable insert	TN.. 2204..
Shank size	32 mm
Pin	259049 2
Clamping claw	259038 13
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of screws10 pieces Type 2	259023 2
Shim Type 33	259031 33
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Clamping claw Type 13	259038 13
Pin Type 2	259049 2
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500