Garant

Clamp toolholder, right-hand, Shank / insert size: 25/15mm

Order data

Order number	250608 25/15
GTIN	4045197650450
Item class	21T

Technical description

suitable indexable insert	DN.. 1506..
Shim	259031 28
Shim screw	259025 10
Shank size	25 mm
Functional width L_4	32 mm
ISO code toolholder	DDJNR/L 2525M15
Clamp, screw, spring	259035 2
Insert size	15 mm
Head length L_1	36 mm
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Shim screw Type 10	259025 10
Shim Type 28	259031 28
Clamp unit Type 2	259035 2
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500