Clamp toolholder, left-hand, Shank / insert size: 20/15mm

Order data

Order number	250609 20/15
GTIN	4045197650467
Item class	21T

Technical description

Shim	259031 28
Shank size	20 mm
Functional width L_4	25 mm
Shim screw	259025 10
Insert size	15 mm
suitable indexable insert	DN.. 1506..
Head length L_1	35 mm
ISO code toolholder	DDJNR/L 2020K15
Clamp, screw, spring	259035 2
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar

Accessories

Clamp unit Type 2	259035 2
Shim screw Type 10	259025 10
Shim Type 28	259031 28
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500