Underwater Kinetics

LED-EX torch with batteries, Type: 4AAZOOM

Order data

Order number	081521 4AAZOOM
GTIN	032705145410
Item class	08C

Description

Version:
Explosion-proof torch, tested to the applicable ATEX guidelines.
High-performance LED lamps shock-resistant, dust-proof and waterproof.
With **LED reflector technology. LED hand lamp and helmet lamp with zoom function.** Beam of light can be focused (beam 16° – 33°). Patented optical system.
Function:
IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Illumination time	8 h
Number of batteries contained	4
Colour of housing	yellow
Head ∅	35 mm
Illumination	130 - 165 lm
ATEX zone	zone 20
ATEX zone	zone 0
Battery type	Mignon, AA
Weight	176 g
IP Index of Protection	IP 67

Overall length	170 mm
Tool properties	Suitable for EX areas
Illumination range	100 m
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR6	081551 LR6
Alkaline-manganese batteries International size LR6	081552 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081554 LR6
Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081561 LR6