EROGLU Präzisionswerkzeuge

OZ collet chuck, SK 50, Clamping range: 4-32mm

Order data

Order number	302462 4-32
GTIN	4250122600060
Item class	36E

Description

Version:
Ball-bearing power-clamping nut.
Application:
For clamping tools with plain shank in OZ collets to ISO 10897.
Optional extras:
OZ collets No. 309540 – 309560, Set No. 309562 (type 462 E) for size 2 – 25, C wrench No. 628400.

Technical description

Suitable C-hook (pin) spanner No. 628400	68/75
Spare clamping nut No. 309670	4 - 32
Clamping range	4 - 32 mm
Overhang dimension A	73 mm
Thread M	M24
Overall length L	200 mm
External ∅ D	72 mm
Clamping ∅ D_1	4-32 mm
Adapter	SK 50
Arbor standard	DIN 2080

Concentricity	≤ 3 µm
Type of product	Collet chuck

Accessories

OZ collet for chuck Nominal clamping ∅ d 25 mm	309560 25
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
OZ collet for chuck Nominal clamping ∅ d 16 mm	309560 16
Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studForm A suitable for steep tapers 50	308600 50
OZ collet for chuck Nominal clamping ∅ d 22 mm	309560 22
OZ collet for chuck Nominal clamping ∅ d 20 mm	309560 20
Special pull stud with internal thread suitable for steep tapers 50	308740 50
OZ clamping nut Clamping chuck clamping range 4-32 mm	309670 4-32
Pull studsealed suitable for steep tapers 50	308660 50
OZ collet for chuck Nominal clamping ∅ d 14 mm	309560 14
Pull studForm B suitable for steep tapers 50	308640 50
OZ collet for chuck Nominal clamping ∅ d 10 mm	309560 10
OZ collet for chuck Nominal clamping ∅ d 18 mm	309560 18

OZ collet for chuck Nominal clamping ∅ d 12 mm	309560 12
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
OZ collet for chuck Nominal clamping ∅ d 32 mm	309560 32
OZ collet for chuck Nominal clamping ∅ d 30 mm	309560 30
OZ collet for chuck Nominal clamping ∅ d 28 mm	309560 28
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
C-hook (pin) spannerwith square pin for external nut ∅ 68/75 mm	628400 68/75
Pull stud 45°sealed suitable for steep tapers 50	308760 50