Screw-on toolholder, left-hand, Shank / insert size: 20/11mm

Order data

Order number	261309 20/11
GTIN	4045197655936
Item class	21T

Technical description

ISO code toolholder	SVHCR/L 2020K11
Shank size	20 mm
Functional width L_4	25 mm
Pack of insert screws	269028 22
Head length L_1	17 mm
suitable indexable insert	VC.. 1103..
Insert size	11 mm
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 22	269028 22
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500